


Series 1200

Minigraph Recorders Temperature and Process Inputs



Minigraph Recorders combine compact size, durability, accuracy and low cost for an exceptional value. Units are widely used in applications ranging from commercial, industrial, and process to laboratory, field, marine, aerospace and more.

Series 1200 Minigraph Recorders use a unique stylus which records on special pressure sensitive paper. No messy ink pens, reservoirs or ink cartridges are used, eliminating maintenance problems and data loss caused by dry pens.

Stock temperature recorders come complete with 6" long x 3/16" dia. K type thermocouple protected by a 304 SS sheath with 8 ft. fiberglass insulated cable. They will record a full 31 days of information on a single 62 ft. x 2-9/16" wide paper roll. Stock units operate from a 120 VAC power source; special units are available for 240 VAC or 12 VDC.

Model	Range	Input Type
1201-11-09-04	0-100 mV	DC Voltage
1201-12-09-04	0-1V	DC Voltage
1201-20-09-04	4-20 mA	DC Current
1201-21-09-04	4-20 mA	0-14 PH
1202-05-09-04	0-200°F	Type K T/C
1202-12-09-04	0-1000°F	Type K T/C
1203-01-09-04	-20 to 130°F	Thermistor
1204-05-09-04	0-300 V	AC Voltage

SPECIFICATIONS

Pen Response Speed: 1 second full scale. Stylus strikes chart once in two seconds. Dot density depends on chart speed.

Temperature Limits: 32 to 122°F (0 to 50°C).

Accuracy: ±2% of span for DC and temperature inputs: ±3% of span for AC inputs.

Power Supply: Standard: 120 VAC. 60 Hz. 3W nominal: Optional: 240 VAC. 60 Hz. 3W nominal or 12 VDC. 20 mA nominal.

Chart Size: 2-9/16" wide x 62' long. 2-1/8" active width (65 mm wide x 19 m long, 54 mm active width).

Housing Size: 3-5/8" wide x 5-5/8" height x 4-5/8" depth. (92 mm wide x 143 mm height x 111 mm depth). Weight: 3-1/2 lb (1.6 kg).

Charts (Packed 6 per box)

Parts No.	Major/Minor Division	
MG651-691630	8/40	
MG651-691760	10/50	
MG651-691770	15/75	
MG651-691950	10/47	
MG651-691650	12/60	
MG651-220920	14/70	

Distributed By: M&M Control Service, Inc. www.mmcontrol.com/Love Controls.php